#### 504009

Fecha de Alta 13-08-2021 Versión

## MONTOSPRAY PREFILL



4 - 17/09/2024



FAMILY ESMALTES

LINE SPRAY MULTISOPORTE

#### **DESCRIPTION AND NATURE**

Container loaded with propellant, solvents and additives to be filled with solvent paints. Compatible with most paints, guaranteeing correct application. Ideal for repairing specific points or repainting specific areas.

The loaded product is not modified, so its properties align with those defined in its Technical Data Sheet.

Tested with Montosisntétic, Marisma, Fast Drying Enamel, Luxatin, Ferrorite, Synthetic Varnishes, Montoxyl Classic, Teak Oil...for other products please consult.

#### **USAGES**

#### **PROPERTIES**

### **TECHNICAL CHARACTERISTCS**

Referencia Color MONTOSPRAY PREFILL

### SURFACE PREPAIRING

#### **New surfaces**

Follow the indications of the filled product.

#### Restoring and maintenance

Follow the indications of the filled product.

### WAY OF USE

#### **Application notes**

Shake the container vigorously for about 2 minutes to homogenise its contents perfectly.

Carry out application tests in a non-visible place.

Protect areas that are not to be painted.

Apply at a distance of 25-30cm from the surface in light, criss-cross strokes.

Do not apply the product at high temperatures, or on surfaces exposed to strong sunlight.

Maintain good ventilation conditions during the drying time.

Do not apply while the relative humidity is above 80%.

Do not use at temperatures below 15°C.

When finished, empty the contents of the cannula by dosing with the container upside down.

### Solvent for dilution and cleaning

Solvent 1406-05

Way of use

**Aproximate dilution** 

#### 504009

# MONTOSPRAY PREFILL

Fecha de Alta 13-08-2021 Versión

4 - 17/09/2024



### SYSTEM

Procedures depending of surface type

Primer Intermedium Finish

### **SECURITY**

Do not eat, neither drink, nor smoke during the application. In case of contact with eyes, wash abundantly with clean water. Keep away from children. Do not throw in darin. Keep product in dry area, under cover and temperature between 5 to 35°C. For further information, please check product safety sheet.

### NOTE

Maximum recommended storage time: 48 months since its fabrication in its original packaging perfectly closed, stored indoors and at temperatures between  $5^{\circ}$  and  $35^{\circ}$ C

Information here indicated is based on our actual knowledge, laboratory testing and taking in count the practical use under specific circumstances. As it is impossible to stablish an adecuate description for every nature and status of the supports to be painted, we are unable to warrant the absolute reproductibility in each specific use

### PACKINGS

0.4 L